



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

## 瑞士梅特勒-托利多电子天平价格

河南兄弟仪器设备有限公司提供最新的瑞士梅特勒-托利多价格最新报价单, 向广大用户供应性能稳定、技术先进、售后服务完善的电子天平产品, 欢迎来电咨询瑞士梅特勒-托利多最新优惠价格。兄弟竭诚为您服务!!

分析天平				
系列	型号	订货号	最大称重/精度	价格
AL 分析天平	AL104	1220511-CN	110g/0.1mg	-
	AL204	12120512-CN	210g/0.1mg	-
AL-IC 分析天平	AL104-IC	12120800-CN	110g/0.1mg	-
	AL204-IC	12120802-CN	220g/0.1mg	-
ML 分析天平	ML54	11143990-CN	52g/0.1mg	-
	ML104	11143996-CN	120g/0.1mg	-
	ML204	11144002-CN	220g/0.1mg	-
MS 分析天平	MS 105	11142056	120g/0.01mg	-
	MS 105DU	11142062	42g/0.01mg; 120g/0.1mg	-
	MS 205DU	11142068	82g/0.01mg; 220g/0.1mg	-
	MS 104S	11124474	120g/0.1mg	-
	MS 204S	11124477	220g/0.1mg	-
	MS 304S	11124480	320g/0.1mg	-
XS 微量分析天平	XS3DU	11122445	800mg/1ug; 3.1g/10ug	-
	XS105DU	11106009	41g/0.01mg; 120g/0.1mg	-
	XS205DU	11106000	81g/0.01mg; 220g/0.1mg	-
	XS64	11106015	61g/0.1mg	-
	XS104	11106012	120g/0.1mg	-
	XS204	11106003	220g/0.1mg	-
	XS204DR	11106006	81g/0.1mg; 220g/1mg	-
XP 分析天平	XP205	11106024	220g/0.01mg	-
	XP105DR	11106036	31g/0.01mg; 120g/0.1mg	-
	XP205DR	11106027	81g/0.01mg; 220g/0.1mg	-
	XP204	11106030	220g/0.1mg	-
	XP504	11106042	520g/0.1mg	-
	XP504DR	11106045	101g/0.1mg; 520g/1mg	-
XPU 微量天平	XP6U	11122400	6.1g/0.1ug	-
	XP2U	11122430	2.1g/0.1ug	-
	XP6	11122415	6.1g/1ug	-
XP 微量天平	XP26	11106048	22g/1ug	-
	XP26DR	11106051	5.1g/2ug; 22g/0.01mg	-
	XP56	11106054	52g/1ug	-



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

XP56DR	11106057	11g/2ug: 52g/0.01mg	-
--------	----------	---------------------	---

-

<b>精密天平</b>				
系列	型号	订货号	最大称重/精度	价格
PL-L 便携式天平	PL202-L	12106440-CN	210g/0.01g	-
	PL402-L	12106445-CN	410g/0.01g	-
	PL602-L	12106450-CN	610g/0.01g	-
	PL601-L	12106455-CN	610g/0.1g	-
	PL1001-L	12106460-CN	1100g/0.1g	-
	PL2001-L	12106465-CN	2100g/0.1g	-
	PL4001-L	12106470-CN	4100g/0.1g	-
	PL6001-L	12106475-CN	6100g/0.1g	-
	PL6000-L	12106480-CN	6100g/1g	-
PL 精密天平	PL203	12120560-CN	210g/0.001g	-
	PL303	12120514-CN	310g/0.001g	-
	PL403	12120561-CN	410g/0.001g	-
	PL2002	12120562-CN	2100g/0.01g	-
	PL3002	12120516-CN	3100g/0.01g	-
	PL4002	12120563-CN	4100g/0.01g	-
	PL4001	12120517-CN	4100g/0.1g	-
PL-IC 精密天平	PL203-IC	12120803-CN	210g/0.001g	-
	PL303-IC	12120804-CN	310g/0.001g	-
	PL403-IC	12120805-CN	410g/0.001g	-
	PL2002-IC	12120806-CN	2100g/0.01g	-
	PL3002-IC	12120807-CN	3100g/0.01g	-
	PL4002-IC	12120808-CN	4100g/0.01g	-
ML 精密天平	ML203	11144029-CN	220g/0.001g	-
	ML203E	11144035-CN	220g/0.001g	-
	ML303	11144038-CN	320g/0.001g	-
	ML303E	11144044-CN	320g/0.001g	-
	ML503	11144056-CN	520g/0.001g	-
	ML802	11144080-CN	820g/0.01g	-
	ML802E	11144083-CN	820g/0.01g	-
	ML1502E	11144095-CN	1520g/0.01g	-
	ML1602	11144092-CN	1620g/0.01g	-
ML3002	11144104-CN	3200g/0.01g	-	



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

<a href="#">ML3002E</a>	<a href="#">11144107-CN</a>	<a href="#">3200g/0.01g</a>	-
<a href="#">ML4002</a>	<a href="#">11144110-CN</a>	<a href="#">4200g/0.01g</a>	-
<a href="#">ML4002E</a>	<a href="#">11144113-CN</a>	<a href="#">4200g/0.01g</a>	-
<a href="#">ML2001</a>	<a href="#">11144122-CN</a>	<a href="#">2200g/0.1g</a>	-
<a href="#">ML4001</a>	<a href="#">11144134-CN</a>	<a href="#">4200g/0.1g</a>	-
<a href="#">ML6001</a>	<a href="#">11144146-CN</a>	<a href="#">6200g/0.1g</a>	-
<a href="#">ML6001E</a>	<a href="#">11144149-CN</a>	<a href="#">6200g/0.1g</a>	-

-

## 精密天平 II

系列	型号	订货号	最大称重/精度	价格
MS 精密天平	<a href="#">MS303S</a>	<a href="#">11124489</a>	<a href="#">320g/0.001g</a>	-
	<a href="#">MS303SE</a>	<a href="#">11124611</a>	<a href="#">320g/0.001g</a>	-
	<a href="#">MS403S</a>	<a href="#">11124492</a>	<a href="#">420g/0.001g</a>	-
	<a href="#">MS603S</a>	<a href="#">11124498</a>	<a href="#">620g/0.001g</a>	-
	<a href="#">MS1003S</a>	<a href="#">11124504</a>	<a href="#">1020g/0.001g</a>	-
	<a href="#">MS1602S</a>	<a href="#">11124516</a>	<a href="#">1620g/0.01g</a>	-
	<a href="#">MS1602SE</a>	<a href="#">11124629</a>	<a href="#">1620g/0.01g</a>	-
	<a href="#">MS3002S</a>	<a href="#">11124522</a>	<a href="#">3200g/0.01g</a>	-
	<a href="#">MS3002SE</a>	<a href="#">11124635</a>	<a href="#">3200g/0.01g</a>	-
	<a href="#">MS4002S</a>	<a href="#">11124528</a>	<a href="#">4200g/0.01g</a>	-
	<a href="#">MS4002SDR</a>	<a href="#">11124531</a>	<a href="#">820g/0.01g4200g/0.1g</a>	-
	<a href="#">MS6002S</a>	<a href="#">11124537</a>	<a href="#">6200g/0.01g</a>	-
	<a href="#">MS6002SDR</a>	<a href="#">11124540</a>	<a href="#">1220g/0.01g6200g/0.1g</a>	-
	<a href="#">MS6001S</a>	<a href="#">11124561</a>	<a href="#">6200g/0.1g</a>	-
	<a href="#">MS8001S</a>	<a href="#">11124564</a>	<a href="#">8200g/0.1g</a>	-
	<a href="#">MS8001SE</a>	<a href="#">11124662</a>	<a href="#">8200g/0.1g</a>	-
XS EX 天平	<a href="#">XS204SX</a>	<a href="#">11121620</a>	<a href="#">210g/0.1mg</a>	-
	<a href="#">XS603SX</a>	<a href="#">11121626</a>	<a href="#">610g/0.001g</a>	-
	<a href="#">XS1003SX</a>	<a href="#">11121632</a>	<a href="#">1010g/0.001g</a>	-
	<a href="#">XS5003SXDR</a>	<a href="#">11121638</a>	<a href="#">1000g/0.001g5100g/0.01g</a>	-
	<a href="#">XS4002SX</a>	<a href="#">11121644</a>	<a href="#">4100g/0.01g</a>	-
	<a href="#">XS6002SX</a>	<a href="#">11121650</a>	<a href="#">6100g/0.01g</a>	-
	<a href="#">XS4001SX</a>	<a href="#">11121656</a>	<a href="#">4100g/0.1g</a>	-
	<a href="#">XS32001LX</a>	<a href="#">11121704</a>	<a href="#">32100g/0.1g</a>	-
	<a href="#">XS64001LX</a>	<a href="#">11121710</a>	<a href="#">64100g/0.1g</a>	-
	<a href="#">XS32000LX</a>	<a href="#">11121716</a>	<a href="#">32100g/1g</a>	-



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

	<a href="#">XS64000LX</a>	<a href="#">11121722</a>	<a href="#">64100g/1g</a>	-
--	---------------------------	--------------------------	---------------------------	---

[PSX2 11132730 XS Ex 电源适配器所有 XS X 型号需配置2800](#)

-

<b>精密天平 III</b>				
系列	型号	订货号	最大称重/精度	价格
XS S 精密天平	<a href="#">XS203S</a>	<a href="#">11130153</a>	<a href="#">210g/0.001g</a>	-
	<a href="#">XS403S</a>	<a href="#">11130156</a>	<a href="#">410g/0.001g</a>	-
	<a href="#">XS603S</a>	<a href="#">11130159</a>	<a href="#">610g/0.001g</a>	-
	<a href="#">XS603SDR</a>	<a href="#">11130162</a>	<a href="#">120g/0.001g610g/0.01g</a>	-
	<a href="#">XS1003S</a>	<a href="#">11130165</a>	<a href="#">1010g/0.001g</a>	-
	<a href="#">XS802S</a>	<a href="#">11130168</a>	<a href="#">810g/0.01g</a>	-
	<a href="#">XS2002S</a>	<a href="#">11130171</a>	<a href="#">2100g/0.01g</a>	-
	<a href="#">XS4002S</a>	<a href="#">11130174</a>	<a href="#">4100g/0.01g</a>	-
	<a href="#">XS4002SDR</a>	<a href="#">11130177</a>	<a href="#">800g/0.01g4100g/0.1g</a>	-
	<a href="#">XS6002S</a>	<a href="#">11130180</a>	<a href="#">6100g/0.01g</a>	-
	<a href="#">XS6002SDR</a>	<a href="#">11130183</a>	<a href="#">1200g/0.01g6100g/0.1g</a>	-
	<a href="#">XS4001S</a>	<a href="#">11130186</a>	<a href="#">4100g/0.1g</a>	-
	<a href="#">XS6001S</a>	<a href="#">11130189</a>	<a href="#">6100g/0.1g</a>	-
	<a href="#">XS8001S</a>	<a href="#">11130192</a>	<a href="#">8100g/0.1g</a>	-
XP S 精密天平	<a href="#">XP204S</a>	<a href="#">11130052</a>	<a href="#">210g/0.1mg</a>	-
	<a href="#">XP404S</a>	<a href="#">11130076</a>	<a href="#">410g/0.1mg</a>	-
	<a href="#">XP404SDR</a>	<a href="#">11130082</a>	<a href="#">80g/0.1mg410g/1mg</a>	-
	<a href="#">XP203S</a>	<a href="#">11130022</a>	<a href="#">210g/0.001g</a>	-
	<a href="#">XP603S</a>	<a href="#">11130020</a>	<a href="#">610g/0.001g</a>	-
	<a href="#">XP603SDR</a>	<a href="#">11130040</a>	<a href="#">120g/0.001g610g/0.01g</a>	-
	<a href="#">XP1203S</a>	<a href="#">11130000</a>	<a href="#">1210g/0.001g</a>	-
	<a href="#">XP2003SDR</a>	<a href="#">11130088</a>	<a href="#">500g/0.001g2100g/0.01g</a>	-
	<a href="#">XP5003SDR</a>	<a href="#">11130094</a>	<a href="#">1000g/0.001g5100g/0.01g</a>	-
	<a href="#">XP802S</a>	<a href="#">11130061</a>	<a href="#">810g/0.01g</a>	-
	<a href="#">XP1202S</a>	<a href="#">11130070</a>	<a href="#">1210g/0.01g</a>	-
	<a href="#">XP2002S</a>	<a href="#">11130060</a>	<a href="#">2100g/0.01g</a>	-
	<a href="#">XP4002S</a>	<a href="#">11130102</a>	<a href="#">4100g/0.01g</a>	-
	<a href="#">XP4002SDR</a>	<a href="#">11130039</a>	<a href="#">800g/0.01g4100g/0.1g</a>	-
	<a href="#">XP6002S</a>	<a href="#">11130100</a>	<a href="#">6100g/0.01g</a>	-
<a href="#">XP6002SDR</a>	<a href="#">11130101</a>	<a href="#">1200g/0.01g6100g/0.1g</a>	-	



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

	<a href="#">XP8002S</a>	<a href="#">11130201</a>	<a href="#">8100g/0.01g</a>	-
	<a href="#">XP10002S</a>	<a href="#">11130200</a>	<a href="#">10100g/0.01g</a>	-
	<a href="#">XP10002SDR</a>	<a href="#">11130206</a>	<a href="#">2000g/0.01g10100g/0.1g</a>	-
	<a href="#">XP2001S</a>	<a href="#">11130152</a>	<a href="#">2100g/0.1g</a>	-
	<a href="#">XP4001S</a>	<a href="#">11130141</a>	<a href="#">4100g/0.1g</a>	-
	<a href="#">XP6001S</a>	<a href="#">11130140</a>	<a href="#">6100g/0.1g</a>	-
	<a href="#">XP8001S</a>	<a href="#">11130221</a>	<a href="#">8100g/0.1g</a>	-
	<a href="#">XP10001S</a>	<a href="#">11130220</a>	<a href="#">10100g/0.1g</a>	-

-

## 大量程精密天平及快速水分测定仪

系列	型号	订货号	最大称重/精度	价格
MS L	<a href="#">MS12001L</a>	<a href="#">11124573</a>	<a href="#">12200g/0.1g</a>	-
	<a href="#">MS16001L</a>	<a href="#">11124576</a>	<a href="#">16200g/0.1g</a>	-
	<a href="#">MS16001LE</a>	<a href="#">11124671</a>	<a href="#">16200g/0.1g</a>	-
	<a href="#">MS32001L</a>	<a href="#">11124588</a>	<a href="#">32200g/0.1g</a>	-
	<a href="#">MS32001LE</a>	<a href="#">11124683</a>	<a href="#">32200g/0.1g</a>	-
	<a href="#">MS32000L</a>	<a href="#">11124701</a>	<a href="#">32200g/1g</a>	-
	<a href="#">MS32000LE</a>	<a href="#">11124704</a>	<a href="#">32200g/1g</a>	-
XS L	<a href="#">XS8001L</a>	<a href="#">11130660</a>	<a href="#">8100g/0.1g</a>	-
	<a href="#">XS16001L</a>	<a href="#">11130663</a>	<a href="#">16100g/0.1g</a>	-
	<a href="#">XS32001L</a>	<a href="#">11130666</a>	<a href="#">32100g/0.1g</a>	-
	<a href="#">XS32001LDR</a>	<a href="#">11130669</a>	<a href="#">6400g/0.1g32100g/1g</a>	-
	<a href="#">XS16000L</a>	<a href="#">11130672</a>	<a href="#">16100g/1g</a>	-
	<a href="#">XS32000L</a>	<a href="#">11130675</a>	<a href="#">32100g/1g</a>	-
	XPL	<a href="#">XP8001L</a>	<a href="#">11130630</a>	<a href="#">8100g/0.1g</a>
<a href="#">XP16001L</a>		<a href="#">11130633</a>	<a href="#">16100g/0.1g</a>	-
<a href="#">XP32001L</a>		<a href="#">11130636</a>	<a href="#">32100g/0.1g</a>	-
<a href="#">XP32001LDR</a>		<a href="#">11130639</a>	<a href="#">6400g/0.1g32100g/1g</a>	-
<a href="#">XP64001L</a>		<a href="#">11130642</a>	<a href="#">64100g/0.1g</a>	-
<a href="#">XP16000L</a>		<a href="#">11130645</a>	<a href="#">16100g/1g</a>	-
<a href="#">XP32000L</a>		<a href="#">11130648</a>	<a href="#">32100g/1g</a>	-
<a href="#">XP64000L</a>		<a href="#">11130651</a>	<a href="#">64100g/1g</a>	-
-				
快速水分测定	<a href="#">HR83</a>	<a href="#">21470</a>	<a href="#">81g, 0.1mg/1mg, 0.001%/0.01%</a> <a href="#">40-200°C/1°C, 标配 LocalCAN 接口</a>	-



# 河南兄弟仪器设备有限公司

免费服务热线: 400-658-1718

仪	<a href="#">HR83P</a>	<a href="#">214703</a>	技术参数同上(含内置打印机)	-
	<a href="#">HG63</a>	<a href="#">214700</a>	<a href="#">61g, 1mg/0.01%</a> <a href="#">40-200°C/1°C, 标配 LocalCAN 接口</a>	-
	<a href="#">HG63P</a>	<a href="#">214701</a>	技术参数同上(含内置打印机)	-
	<a href="#">HB43-S</a>	<a href="#">11121800</a>	<a href="#">54g, 1mg/0.01%</a> <a href="#">50-200°C/1°C, 标配 RS232接口</a>	-
	<a href="#">MJ33</a>	<a href="#">11121810</a>	<a href="#">35g, 1mg/0.01%</a> <a href="#">50-160°C/1°C, 标配 RS232接口</a>	-

河南兄弟仪器设备有限公司-电子天平事业部

服务热线: 400-658-1718

销售热线: 0371-63738879, 63758879, 63768879

手机热线: 18638219011, 13849116616, 13849119868

天平网址: [www.9yiqi.com](http://www.9yiqi.com)    [www.zgyqsb.com](http://www.zgyqsb.com)